


USER GUIDE

Hot towel cabinet, ref. WARMEX (T-02)

1. General product information



2. Technical specifications

Capacity	11l
Rated Power	200W
Rated Voltage	220V ~ 240V
Frequency	50Hz/60Hz
Maximum temperature	80°C
Dimensions	46x35x31cm

3. Operation

- 1) Fold clean wet towels and place them onto the metallic shelf of the towel cabinet and close the door.

SUN TECHNOLOGIES APS

- 2) Press the power switch to turn the unit on, the working indicator next to the button will be switched on, which shows that the cabinet has started heating.
- 3) When the temperature reaches the maximum temperature, it will get stopped.
- 4) If you need to take the towels out, switch the unit off and the LED indicator will turn off. It is recommended to use tweezers to take the towels out so as to avoid being burnt.

4. Remarks

- Place the unit in a cool and dry place far from inflammable spaces. It is recommended to keep 30 mm at least from the other objects nearby.
- Select a proper socket according to the technical specifications above.
- This unit is conceived for heating the towels, not drying them, so avoid placing them completely soaked into the cabinet. This will extend the unit lifespan.
- Do not open the cabinet door while working.
- Do not introduce chemical substances into the cabinet.
- If any incidence happens to the unit during operation, switch it off and inform either the manufacturer or a qualified professional. Do not manipulate it without the manufacturer permission.
- Clean the cabinet with a neutral product regularly. Do not use acidic or alkaline chemical products which can become corrosive or toxic for the unit.
- Switch it off and unplug the unit if you are not using it.